

Product Specification:



- Satin Finish 320 Grit Polished giving an Ra value of less than 0.5
- Suitable for Cleanroom, sterile rooms, food processing and research areas.
- No dirt traps
- Ideal for gowning room apparel such as garments, hairnets, gloves, hoods and shoe covers.

Product Dimensions:

Reference	Height	Width	Depth
KRGC2500	2500mm	1200mm	500mm
KRGC2000	2000mm	1200mm	500mm
KRGC1800	1800mm	1200mm	500mm

Overview:

The Kent Stainless recessed gowning cabinet is designed to be easily cleaned with tight, smooth joints to wall and floor finished. This creates ledge and crevice free surfaces.

These recess units have excellent hygienic properties and are virtually maintenance free.

Options:

Stainless Steel Grade	Finish	Thickness	Shelves	Hangers
304	Bead Blasted	2mm	1	Loose
316	Satin Finish 320 Grit Polished	3mm	2	Set in position
	Electropolished		3	Not required
	Bead Blasted & Electropolished		4	
	Satin Finish 320 Grit Polished & Electropolished			
	Powder Coated			

Maintenance:

Stainless Steel:

Clean the stainless steel components using warm water with a mild detergent with a non abrasive cloth or sponge. Heavier stains may require the use of a nylon scouring pad or a stainless steel cleaner. To remove paint or graffiti use a cloth and Alkaline or solvent paint strippers according to type of paint. In the case of a bead blasted finish, where abrasive cleaning is required, always use a random circular rubbing action with a cloth. In the case of brushed finishes the surface consists of uniform fine 'scratches' running in one direction so where abrasive cleaning is required always use a straight back and forward rubbing action in the direction of the grain using soap and warm water. Rust spots or 'tea stains' can occur on the surface of the material, these are normally caused by contamination from ordinary mild steel, particularly in areas where construction work has been undertaken. Such stains can be removed using Rust Remover 410. In cases where the surface is severely stained as a result of severe environmental conditions or scratched due to misuse, it may still be possible to restore the original finish using chemicals such as Oxalic Acid solution. There are many stainless steel polishes available to enhance the surface finish. We recommend [Mister Stainless Ltd.](#) as a provider for stainless steel cleaning products